



□□□□□

## Eaton 170M6359

Fuse-link, high speed, 550 A, AC 690 V, size 3,  
76 x 92 x 126 mm, aR, IEC, single indicator

□□□□

|                                 |                                                         |
|---------------------------------|---------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Bussmann series<br>high speed square body<br>fuse |
| <b>CATALOG NUMBER</b>           | 170M6359                                                |
| <b>UPC</b>                      | 051712263962                                            |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 78 mm                                                   |
| <b>PRODUCT HEIGHT</b>           | 123 mm                                                  |
| <b>PRODUCT WIDTH</b>            | 155 mm                                                  |
| <b>PRODUCT WEIGHT</b>           | 694 g                                                   |
| <b>COMPLIANCES</b>              | CE Marked<br>RoHS Compliant                             |
| <b>CERTIFICATIONS</b>           | UL Recognized<br>IEC Rated                              |

□□□□

|                                          |                                                                      |
|------------------------------------------|----------------------------------------------------------------------|
| AMPERAGE RATING                          | 550 A                                                                |
| BREAKING CAPACITY                        | 200 kA                                                               |
| FUSE INDICATOR                           | Centre fuse status indicator                                         |
| INSULATED METAL GRIPPING LUGS (IMGL)     | No                                                                   |
| UTILIZATION CATEGORY                     | aR (accompanied semiconductor protection)                            |
| VOLTAGE TYPE                             | AC                                                                   |
| FUSE SIZE                                | 3                                                                    |
| RATED VOLTAGE AC                         | 690 V                                                                |
| CENTER-TO-CENTER DISTANCE OF CONNECTIONS | 91.5 mm                                                              |
| CURRENT TYPE                             | AC                                                                   |
| MOUNTING DIMENSION                       | Other                                                                |
| CLASS                                    | Class aR                                                             |
| CLEARING (I <sub>2</sub> T)              | 135000 at 660 V                                                      |
| WATT LOSSES                              | 100 W                                                                |
| FUSE SHAPE                               | Square body, slotted center bolted tags                              |
| PRE ARC (I <sub>2</sub> T)               | 19500                                                                |
| COLOR                                    | None                                                                 |
| INTERRUPT RATING                         | 200 kAIC                                                             |
| FITTED WITH:                             | Type K Indicator for micro                                           |
| CONSTRUCTION SIZE                        | 3                                                                    |
| PACKAGING TYPE                           | Standard                                                             |
| VOLTAGE RATING                           | 690 V                                                                |
| TYPE                                     | Fuse                                                                 |
| APPLICATION                              | Semiconductor, DC Common bus, DC drives, power converters/rectifiers |
| FUSE TYPE                                | French style EKN/Type K Indicator for Micro Bolted tag               |
| FUSE SYSTEM (ACCORDING TO IEC 60269)     | Other                                                                |

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

