



## Eaton 170M6368

Eaton Bussmann series high speed square body fuse, 1500 A, AC 690 V, size 3, 76 x 92 x 126 mm, aR, IEC, single indicator

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M6368
<b>UPC</b>	051712264051
<b>PRODUCT LENGTH/DEPTH</b>	78 mm
<b>PRODUCT HEIGHT</b>	123 mm
<b>PRODUCT WIDTH</b>	155 mm
<b>PRODUCT WEIGHT</b>	1287 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC Rated UL Recognized



Powering Business Worldwide



<b>AMPERAGE RATING</b>	1500 A
<b>BREAKING CAPACITY</b>	100 kA
<b>FUSE INDICATOR</b>	Non Indicating
<b>UTILIZATION CATEGORY</b>	aR (accompanied semiconductor protection)
<b>FUSE SIZE</b>	3
<b>RATED VOLTAGE AC</b>	690 V
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	126 mm
<b>CURRENT TYPE</b>	AC
<b>MOUNTING DIMENSION</b>	M10
<b>CLASS</b>	Class aR
<b>CLEARING (I2T)</b>	2450000 at 660 V
<b>WATT LOSSES</b>	160 W
<b>PRE ARC (I2T)</b>	460000
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	200 kAIC
<b>CONNECTION</b>	Blade end x blade end
<b>CONSTRUCTION SIZE</b>	3
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	700 V (UL), 690 V (IEC)
<b>TYPE</b>	Square body French style - EKN/ type K indicator for micro
<b>APPLICATION</b>	DC common bus DC drives power converters/rectifiers reduced voltage starters
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other



DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

