

Eaton 170M6452

Eaton Bussmann series high speed square body fuse, 700V (UL), 690V (IEC), 630A, 200 kAIC, None, Fuse, Class aR

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6452
UPC	051712394130
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	86 mm
PRODUCT WIDTH	76 mm
PRODUCT WEIGHT	1247 g
COMPLIANCES	Contact factory RoHS Compliant

AMPERAGE RATING	630 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	690 V
CURRENT TYPE	AC
CLASS	Class aR
WATT LOSSES	105 W
FUSE SHAPE	Square body, knife blade contacts
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	DIN 43620 Bladed
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

