



Eaton 170M6464

Fuse-link, high speed, 1000 A, AC 690 V, size 3, aR, IEC, UL, type K indicator

170M6464

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6464
UPC	051712814423
PRODUCT LENGTH/DEPTH	53 mm
PRODUCT HEIGHT	92 mm
PRODUCT WIDTH	76 mm
PRODUCT WEIGHT	848 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

□□□

AMPERAGE RATING	1000 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	52.4 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M12
CLASS	Class aR
CLEARING (I₂T)	945000 at 660 V
WATT LOSSES	122 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I₂T)	140000
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	3
MOUNTING METHOD	Flush
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end BKN/Type K Indicator for Micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

□□

DECLARATIONS OF CONFORMITY

eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf

□□□□:

四

10

11

EATON
Powering Business Worldwide

□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 00 0000000

