


Eaton 170M6642

Fuse-link, high speed, 700 A, AC 2500 V, size 3, 86 x 95 x 195 mm, aR, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6642
PRODUCT LENGTH/DEPTH	110 mm
PRODUCT HEIGHT	130 mm
PRODUCT WIDTH	207 mm
PRODUCT WEIGHT	291.5 g
COMPLIANCES	CE

AMPERAGE RATING	700 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	2500 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	195 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M12
CLASS	Class aR
WATT LOSSES	155 W
FUSE SHAPE	Square body, flush end contacts
COLOR	None
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	3
VOLTAGE RATING	2500 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Flush end
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

