



Eaton 170M7063

Eaton Bussmann series Fuse-link, high speed, 2500 A, AC 690 V, 200 kA, size 4, 67 x 105 x 105 mm, aR, IEC, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M7063
UPC	051712266475
PRODUCT LENGTH/DEPTH	67 mm
PRODUCT HEIGHT	105 mm
PRODUCT WIDTH	105 mm
PRODUCT WEIGHT	2387 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized



Powering Business Worldwide

□□□□

AMPERAGE RATING	2500 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
TEMPERATURE RATING	>60°C
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	4
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	66.6 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	7800000 at 660 V
WATT LOSSES	275 W
PRE ARC (I2T)	1200000
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	4
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V, 700 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end B/65 Visual indicator
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF CONFORMITY	eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf
□□□□□□□□	170M7063

