



Eaton 170M7156

Fuse-link, high speed, 3000 A, AC 1000 V, size 4, 120 x 105 x 89 mm, aR, IEC, type K indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M7156
UPC	051712295277
PRODUCT LENGTH/DEPTH	89 mm
PRODUCT HEIGHT	120 mm
PRODUCT WIDTH	133 mm
PRODUCT WEIGHT	2689 g
COMPLIANCES	Contact factory RoHS Compliant



Powering Business Worldwide



AMPERAGE RATING	3000 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	4
RATED VOLTAGE AC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	89.4 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	28000000 at 1000 V
WATT LOSSES	380 W
PRE ARC (I2T)	4700000
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	4
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V (IEC)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end SBKN/90 Type K indicator
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



