


## Eaton 170M7400

Eaton Bussmann series Fuse-link, high speed, 315 A, AC 800 V, size NH3, 150 x 76 x 71 mm, gR, IEC, dual indicator

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M7400
<b>UPC</b>	051712712767
<b>PRODUCT LENGTH/DEPTH</b>	76 mm
<b>PRODUCT HEIGHT</b>	150 mm
<b>PRODUCT WIDTH</b>	71.2 mm
<b>PRODUCT WEIGHT</b>	1030 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized

AMPERAGE RATING	315 A
INTERRUPT RATING	65 kAIC
VOLTAGE RATING	800 Vac
WATT LOSSES	44 W



COLOR	White
FUSE TYPE	PV-ANH3
MATERIAL	Ceramic body

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
  
© 2025

Follow us on social media to get the latest product and support information.

