

Eaton 170M7548

Fuse-link, high speed, 1500 A, AC 1000 V, 200 kA, size 4, 100 x 133 x 90 mm, aR, IEC, type K indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M7548
UPC	051712608145
PRODUCT LENGTH/DEPTH	132.5 mm
PRODUCT HEIGHT	90.6 mm
PRODUCT WIDTH	118.2 mm
PRODUCT WEIGHT	0.001 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	1500 A
FUSE INDICATOR	Non Indicating
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	4
CLASS	Class aR
CLEARING (I2T)	3600000 at 1000 V
WATT LOSSES	250 W
FUSE SHAPE	Square body flush end contacts
PRE ARC (I2T)	600000
INTERRUPT RATING	125 kAIC
CONNECTION	Din 43-620 blade end x Din 43-620 blade end
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V (IEC)
TYPE	Square Body, -SBKN/90 type K indicator
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end SBKN/90 Type K indicator

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: