



## Eaton 170M7595

Fuse-link, high speed, 2500 A, AC 1250 V, 200 kA, size 4, 105 x 120 x 110 mm, aR, IEC, type K indicator

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M7595
<b>UPC</b>	051712540438
<b>PRODUCT LENGTH/DEPTH</b>	137.9982 mm
<b>PRODUCT HEIGHT</b>	53.0098 mm
<b>PRODUCT WIDTH</b>	8 mm
<b>PRODUCT WEIGHT</b>	3336 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized IEC Rated

□□□□	
AMPERAGE RATING	2500 A
FUSE INDICATOR	Non Indicating
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	4
CLASS	Class aR
CLEARING (I2T)	28000000 at 1250 V
WATT LOSSES	260 W
PRE ARC (I2T)	4500000
INTERRUPT RATING	125 kAIC 100 kAIC 85 kAIC
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	1250 V (IEC), 1300 V (UL)
TYPE	Square Body flush end contact, -SBKN/105 type K indicator
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end BKN/110 Type K indicator

□□	
DECLARATIONS OF CONFORMITY	<a href="#">eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□: