



Eaton 170M7804

Fuse-link, high speed, 1200 A, AC 1250 V, 200 kA, size 4, 105 x 120 x 110 mm, aR, IEC, type K indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M7804
UPC	051712514538
PRODUCT LENGTH/DEPTH	137.998 mm
PRODUCT HEIGHT	53.01 mm
PRODUCT WIDTH	8 mm
PRODUCT WEIGHT	746 g
CERTIFICATIONS	IEC



Powering Business Worldwide



AMPERAGE RATING	1200 A
BREAKING CAPACITY	180 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	4
RATED VOLTAGE AC	1250 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	110 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	3100000 at 1250 V
WATT LOSSES	240 W
PRE ARC (I2T)	495000
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	4
MOUNTING METHOD	Flush
VOLTAGE RATING	1250 V (IEC), 1300 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end BKN/110 Type K indicator
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)
