



Eaton 170T7025

Fuse-link, high speed, 1600 A, AC 660 V, size 3, 70 x 90 x 147 mm, aR, IEC, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170T7025
PRODUCT LENGTH/DEPTH	90 mm
PRODUCT HEIGHT	74 mm
PRODUCT WIDTH	160 mm
PRODUCT WEIGHT	0.001 g
COMPLIANCES	CE RoHS Compliant EAC
CERTIFICATIONS	IEC 60269-4

□□□□

AMPERAGE RATING	1600 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	660 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	88.8 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M12
CLASS	Class aR
WATT LOSSES	170 W
FUSE SHAPE	Square body, flush end contacts
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	Protection of power rectifiers
FUSE TYPE	Flush end
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

□□

