

Eaton 171277

Eaton Moeller® series SL7 LED multistrobe light, red 24V, H.P.

PRODUCT NAME	Eaton Moeller® series SL7 Multi-strobe light module
CATALOG NUMBER	171277
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	0.089 kg
CERTIFICATIONS	CE
	IEC/EN 60947-5-1
	UL File No.: E29184
	CSA Class No.: NKCR7
	CSA-C22.2 No. 94-91
	UL Category Control No.: NKCR
	CSA-C22.2 No. 14-10
	IEC/EN 60529
	UL report applies to both US and Canada
	Certified by UL for use in Canada
	UL 508
	UL

TYPE	<ul style="list-style-type: none"> High-performance LED for maximum signaling effect Multi-strobe light module
PRODUCT CATEGORY	SL signal towers
POLLUTION DEGREE	3
FLASHING FREQUENCY	1 - 2.6 Hz
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Flash light
COLOR	Red
VOLTAGE TYPE	AC/DC
MATERIAL	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 4 IP66
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	max. 130 mA at 24 V AC/DC
LIFESPAN, ELECTRICAL	50,000 h
LIGHT TYPE	Multistrobe light
LIGHT MODULES	High Performance LED
NUMBER OF MODULES	Max. 5 (with standard base) Max. 10 (with base for mounting on both sides)
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms

DECLARATIONS OF CONFORMITY	DA-DC-00004257.pdf
	DA-DC-00004253.pdf
	IL047004ZU
	eaton-operating-dimensions-005.eps
	eaton-operating-button-symbol-009.eps
	eaton-operating-symbol.eps

RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	26 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	18 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX	30 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	18 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	73 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

