

Eaton 171330

Eaton Moeller® series SL4 Continuous light module, orange, LED, 230 V

PRODUCT NAME	Eaton Moeller® series SL4 Continuous light module
CATALOG NUMBER	171330
PRODUCT LENGTH/DEPTH	43 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	0.043 kg
CERTIFICATIONS	CSA-C22.2 No. 14-10 UL Category Control No.: NKCR IEC/EN 60529 UL report applies to both US and Canada Certified by UL for use in Canada IEC/EN 60947-5-1 UL File No.: E29184 CSA Class No.: NKCR7 UL UL 508 CE CSA-C22.2 No. 94-91

TYPE	Continuous light module
PRODUCT CATEGORY	SL signal towers
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Continuous light
COLOR	Orange
VOLTAGE TYPE	AC
MATERIAL	Enclosure: Polycarbonate (PC) Cap: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 13 IP66
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	34 mA at 230/240 V AC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Continuous light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 5 (with standard base) Max. 10 (with base for mounting on both sides)
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	240 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	230 V

DECLARATIONS OF CONFORMITY	DA-DC-00004253.pdf
	DA-DC-00004257.pdf
	IL047001ZU
	eaton-operating-sl4-continuous-light-dimensions.eps
	eaton-operating-sl7-continuous-light-symbol-002.eps
	eaton-operating-button-sl7-continuous-light-symbol.eps

RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX	0 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	0 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	43 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

