

Eaton 171334

Eaton Moeller® series SL4 Ba15d
continuous light module, white

PRODUCT NAME	Eaton Moeller® series SL4 Continuous light module
CATALOG NUMBER	171334
PRODUCT LENGTH/DEPTH	43 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	0.037 kg
CERTIFICATIONS	Certified by UL for use in Canada CSA Class No.: NKCR7 IEC/EN 60947-5-1 UL CSA-C22.2 No. 14-10 IEC/EN 60529 CSA-C22.2 No. 94-91 CE UL Category Control No.: NKCR UL 508 UL report applies to both US and Canada UL File No.: E29184
CATALOG NOTES	Without light elements

TYPE	Continuous light module
PRODUCT CATEGORY	SL signal towers
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
MOUNTING METHOD	BA15d lamp socket
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Continuous light
COLOR	Other
VOLTAGE TYPE	AC/DC
MATERIAL	Enclosure: Polycarbonate (PC) Cap: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 4X IP66
LAMP TYPE	None
OVERVOLTAGE CATEGORY	III
LIFESPAN, ELECTRICAL	3,000 h
LIGHT TYPE	Continuous light
LIGHT MODULES	Filament lamp max. 4 W
NUMBER OF MODULES	Max. 10 (with base for mounting on both sides) Max. 5 (with standard base)
POWER CONSUMPTION	Max. 4 W with the specified voltages
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	250 V
RATED OPERATIONAL	24 V

DECLARATIONS OF CONFORMITY	DA-DC-00004257.pdf
	DA-DC-00004253.pdf
	IL047005ZU
	eaton-operating-sl4-continuous-light-dimensions.eps
	eaton-operating-button-sl7-continuous-light-symbol-003.eps
	eaton-operating-sl7-continuous-light-symbol.eps

VOLTAGE (UE) AT AC - MIN	
RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX	250 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	24 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	43 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

