



□□□□□

Eaton 171381

Eaton Moeller® series SL4 Acoustic module;230 V;continuous or pulsed tone

□□□□

PRODUCT NAME	Eaton Moeller® series SL4 Acoustic module
CATALOG NUMBER	171381
PRODUCT LENGTH/DEPTH	43 mm
PRODUCT HEIGHT	72 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	0.046 kg
CERTIFICATIONS	Certified by UL for use in Canada IEC/EN 60529 CSA Class No.: NKCR7 CSA-C22.2 No. 14-10 CE UL File No.: E29184 IEC/EN 60947-5-1 UL UL report applies to both US and Canada CSA-C22.2 No. 94-91 UL 508 UL Category Control No.: NKCR

□□□□

TYPE	Acoustic module
PRODUCT CATEGORY	SL signal towers
FREQUENCY RATING	4000 Hz
POLLUTION DEGREE	3
ALARM TYPE	Internal sound setting, 1 pole DIP Tone adjustable 2 types of sound Pulsed tone Continuous tone
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
FUNCTIONS	Continuous tone/pulse tone
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	43 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V
RATED OPERATIONAL CURRENT (IE) - MAX	21 mA
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	240 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	230 V
COLOR	Black
VOLTAGE TYPE	AC
MATERIAL	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
MOUNTING POSITION	As required Place only at the highest position on a pole
DEGREE OF PROTECTION	NEMA 13 IP66

□□

DECLARATIONS OF CONFORMITY	eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf
□□□□□	IL047001ZU
	eaton-operating-sl4-acoustic-module-dimensions.eps
	eaton-operating-sl7-acoustic-module-symbol-002.eps
□□	eaton-operating-sl7-acoustic-module-symbol.eps
	eaton-operating-sl4-acoustic-module-3d-drawing.eps
	eaton-operating-button-sl7-base-module-symbol.eps

OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	0.021 A, at 230/240 V AC
LOUDNESS	80 dB
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

