



□□□□□

Eaton 171463

Eaton Moeller® series SL7 Continuous light module, red, LED, 24 V

□□□□

PRODUCT NAME	Eaton Moeller® series SL7 Continuous light module
CATALOG NUMBER	171463
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	0.08 kg
CERTIFICATIONS	Certified by UL for use in Canada IEC/EN 60529 UL 508 UL report applies to both US and Canada CSA-C22.2 No. 14-10 CSA Class No.: NKCR7 IEC/EN 60947-5-1 CSA-C22.2 No. 94-91 CE UL File No.: E29184 UL Category Control No.: NKCR UL

□□□□

TYPE	Continuous light module
PRODUCT CATEGORY	SL signal towers
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Continuous light
COLOR	Red
VOLTAGE TYPE	AC/DC
MATERIAL	Enclosure: Polycarbonate (PC) Cap: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP66 NEMA 4X
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	50 mA at 24 V AC/DC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Continuous light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 10 (with base for mounting on both sides) Max. 5 (with standard base)
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	24 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	24 V
RATED OPERATIONAL VOLTAGE (UE) AT DC -	24 V

□□

DECLARATIONS OF CONFORMITY	eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf
□□□□□	IL047004ZU
	eaton-operating-dimensions-005.eps
□□	eaton-operating-button-symbol-009.eps
	eaton-operating-sl7-continuous-light-symbol-002.eps

MAX	
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	24 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	73 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4, Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

