

Eaton 171466

Eaton Moeller® series SL7 Continuous light module, orange, LED, 24 V

PRODUCT NAME	Eaton Moeller® series SL7 Continuous light module
CATALOG NUMBER	171466
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	0.08 kg
CERTIFICATIONS	UL File No.: E29184 CSA-C22.2 No. 14-10 IEC/EN 60529 Certified by UL for use in Canada UL UL 508 UL report applies to both US and Canada CSA Class No.: NKCR7 CSA-C22.2 No. 94-91 CE IEC/EN 60947-5-1 UL Category Control No.: NKCR

TYPE	Continuous light module
PRODUCT CATEGORY	SL signal towers
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Continuous light
COLOR	Orange
VOLTAGE TYPE	AC/DC
MATERIAL	Enclosure: Polycarbonate (PC) Cap: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 4 IP66
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	50 mA at 24 V AC/DC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Continuous light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 5 (with standard base) Max. 10 (with base for mounting on both sides)
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	24 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	24 V

DECLARATIONS OF CONFORMITY	DA-DC-00004257.pdf
	DA-DC-00004253.pdf
	IL047004ZU
	eaton-operating-dimensions-005.eps
	eaton-operating-sl7-continuous-light-symbol-002.eps
	eaton-operating-button-sl7-continuous-light-symbol.eps

RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX	24 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	24 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	73 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

