

Eaton 179292

Eaton Moeller® series M22 Potentiometer,
Classical, M22, 22.5 mm, Bezel: titanium

PRODUCT NAME	Eaton Moeller® series M22 Potentiometer
CATALOG NUMBER	179292
PRODUCT LENGTH/DEPTH	48 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.019 kg
CERTIFICATIONS	IEC/EN 60947 CSA File No.: 2324643 CSA Class No.: 3211-07 CSA UL File No.: E29184 UL Category Control No.: NKCR UL

TYPE	Potentiometer
ELECTRIC CONNECTION TYPE	Screw connection
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	Yes
BEZEL COLOR	Titanium
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
NUMBER OF REVOLUTIONS - MAX	1
NUMBER OF REVOLUTIONS - MIN	1
OPENING DIAMETER	22.5 mm
DESIGN	Classical
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP65 NEMA Other
FUNCTIONS	For connecting to SmartWire-DT
POWER CONSUMPTION	0 W
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
RESISTANCE	0 Ohm

IL04716004Z2021_10.pdf	
eaton-operating-m30-potentiometer-wiring-diagram.eps	
eaton-operating-potentiometer-m22-dimensions-002.eps	
eaton-operating-potentiometer-m22-3d-drawing.eps	
/	RMQ small E-Stop emergency-stop button

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

