



□□□□

Eaton 181619

Eaton Moeller® series C22 Indicator light, Flat, Cable (black) with M12A plug, 4 pole, 0.5 m, Lens Blue, LED Blue, 24 V AC/DC

□□□□

PRODUCT NAME	Eaton Moeller® series C22 Indicator light
CATALOG NUMBER	181619
PRODUCT LENGTH/DEPTH	561 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.043 kg
CERTIFICATIONS	UL File No.: E29184 CSA Class No.: 321103 IEC/EN 60947-5-1 UL 508 CE CSA UL CSA-C22.2 No. 14-05 and 94-M91 UL Category Control No.: NKCR VDE 0660 CSA File No.: 165628



Powering Business Worldwide

□□□□

TYPE	Indicator lights
PRODUCT CATEGORY	RMQ compact solution
ELECTRIC CONNECTION TYPE	Other
FITTED WITH:	Front ring Light source
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	800 V AC
BEZEL COLOR	Other
CABLE MATERIAL	PUR
LAMP SOCKET TYPE	LED
ACTUATOR DIAMETER	4.7 mm
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
NUMBER OF PILOT LIGHTS	1
OPENING DIAMETER	22.5 mm
RATED INSULATION VOLTAGE (UI)	30 V
RATED OPERATIONAL VOLTAGE (UE) - MAX	24 V
BEZEL MATERIAL	Plastic
DEGREE OF PROTECTION	IP Other NEMA Other
LENS COLOR	Blue
VOLTAGE TYPE	AC/DC
DESIGN	M12A Flat
MOUNTING POSITION	As required
LIGHT COLOR	Blue
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
RATED OPERATIONAL VOLTAGE (UE) - MIN	24 V
OVERVOLTAGE	III

□□

DECLARATIONS OF CONFORMITY	eaton-pushbutton-declaration-of-conformity-uk250928en.pdf
□□□□□	IL047016ZU
□□□	eaton-operating-c22-indicator-light-wiring-diagram-002.eps
□□	eaton-operating-c22-indicator-light-dimensions-002.eps eaton-operating-button-symbol-003.eps eaton-operating-c22-indicator-light-3d-drawing-002.eps

