

Eaton 183287

Eaton Moeller® series M30 Indicator light,
RMQ-Titan, Flat, white, Metal bezel

PRODUCT NAME	Eaton Moeller® series M30 Indicator light
CATALOG NUMBER	183287
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	32 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	0.035 kg
CERTIFICATIONS	IEC/EN 60947 VDE 0660

TYPE	Indicator lights
FITTED WITH:	Front ring
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	With SWD-RMQ connections Yes
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
BEZEL COLOR	Chrome
SHOCK RESISTANCE	Not planned
BEZEL MATERIAL	Metal
TERMINAL CAPACITY	0.5 - 1.5 mm ² , stranded 0.5 - 1.5 mm ² , solid
LENS COLOR	White
DESIGN	Flat
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION	NEMA 4X, 13
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
FORCE FOR POSITIVE OPENING - MIN	0 N
OPENING DIAMETER	30 mm
OPENING HEIGHT	30 mm
RATED INSULATION VOLTAGE (UI)	250 V
SUITABLE FOR NUMBER OF BUILT-IN SIGNAL LIGHTS	1
WIDTH OPENING	0 mm
PRODUCT CATEGORY	RMQ-Titan
SIZE	Front dimensions: Ø 36 mm
DEGREE OF PROTECTION (FRONT SIDE)	IP67/IP69K
LENS TYPE	Flat

DECLARATIONS OF CONFORMITY	DA-DC-00004135.pdf
	DA-DC-00004157.pdf
	eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf
	eaton-operating-m30-dimensions-005.eps
	eaton-operating-m30-dimensions-006.eps
	eaton-operating-m30-dimensions-004.eps
	eaton-operating-m30-indicator-light-dimensions.eps
	eaton-operating-m30-indicator-light-3d-drawing.eps
	eaton-operating-button-symbol-013.eps
	RMQ small E-Stop emergency-stop button
/	

Round

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

