



□□□□

## Eaton 183289

Eaton Moeller® series M30 Indicator light, RMQ-Titan, Flat, green, individual facility for inscription, Metal bezel

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series M30 indicator light
<b>CATALOG NUMBER</b>	183289
<b>PRODUCT LENGTH/DEPTH</b>	36 mm
<b>PRODUCT HEIGHT</b>	32 mm
<b>PRODUCT WIDTH</b>	46 mm
<b>PRODUCT WEIGHT</b>	0.035 kg
<b>CERTIFICATIONS</b>	IEC/EN 60947 VDE 0660



Powering Business Worldwide

□□□□

<b>TYPE</b>	Indicator lights
<b>FITTED WITH:</b>	Front ring
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>CONNECTION TO SMARTWIRE-DT</b>	With SWD-RMQ connections Yes
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4000 V AC
<b>BEZEL COLOR</b>	Chrome
<b>SHOCK RESISTANCE</b>	Not planned
<b>BEZEL MATERIAL</b>	Metal
<b>TERMINAL CAPACITY</b>	0.5 - 1.5 mm <sup>2</sup> , stranded 0.5 - 1.5 mm <sup>2</sup> , solid
<b>LENS COLOR</b>	Green
<b>DESIGN</b>	Flat
<b>MOUNTING POSITION</b>	As required
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DEGREE OF PROTECTION</b>	NEMA 4X, 13
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>FORCE FOR POSITIVE OPENING - MIN</b>	0 N
<b>OPENING DIAMETER</b>	30 mm
<b>OPENING HEIGHT</b>	30 mm
<b>RATED INSULATION VOLTAGE (UI)</b>	250 V
<b>SUITABLE FOR NUMBER OF BUILT-IN SIGNAL LIGHTS</b>	1
<b>PRODUCT CATEGORY</b>	RMQ-Titan
<b>SIZE</b>	Front dimensions: Ø 36 mm
<b>DEGREE OF PROTECTION (FRONT SIDE)</b>	IP67/IP69K
<b>INSCRIPTION</b>	Individual inscription possible
<b>LENS TYPE</b>	Flat Round

□□

[eaton-operating-m30-indicator-light-dimensions.eps](#)

[eaton-operating-m30-dimensions-005.eps](#)

[eaton-operating-m30-dimensions-006.eps](#)

□□

[eaton-operating-m30-dimensions-004.eps](#)

[eaton-operating-button-symbol-004.eps](#)

[eaton-operating-m30-indicator-light-3d-drawing.eps](#)

