

Eaton 183978

Eaton Moeller series IZMX/INX - ACB.
Connection 3p vertikal

PRODUCT NAME	Eaton Moeller series IZMX/INX main terminal
CATALOG NUMBER	183978
PRODUCT LENGTH/DEPTH	115 mm
PRODUCT HEIGHT	45 mm
PRODUCT WIDTH	60 mm
PRODUCT WEIGHT	7.5 kg
COMPLIANCES	RoHS conform

USED WITH	IZMX40...3...40F
	INX40...3...40W
	IZMX40...3...40W
	Three-pole
	INX40...3...40F
AMPERAGE RATING	4000 A
ACCESSORY/SPARE PART TYPE	Main terminal kits
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
TYPE	Accessory
SPECIAL FEATURES	• Main terminals are not supplied as standard with the basic devices and cassettes. • Each set includes the connections for top and bottom. 3-pole= 6 connections • 4-pole= 8 connections, including accessories for mounting on the flanged circuit-breaker connection. • This connector kit includes L-shaped adapters for all main terminals. • This connector kit is only intended for the 4000 A vertical terminal.
SUITABLE FOR	Three-pole

	eaton-izmx-type-rf-rear-primary-adapter-il01301053e.pdf
	eaton-circuit-breaker-izmx-inx-main-terminal-dimensions-018.eps
	eaton-circuit-breaker-izmx-inx-main-terminal-dimensions-017.eps
	eaton-circuit-breaker-izmx-inx-main-terminal-3d-drawing.eps

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

