

## Eaton 184116

Eaton Moeller series IZMX/INX - ACB.  
Accessories, Trip-indicating auxiliary switch,  
"Triggered" signaling contact with two  
changeover contacts, For use with IZMX16...,  
IZMX40...

<b>PRODUCT NAME</b>	Eaton Moeller series IZMX/INX - ACB
<b>CATALOG NUMBER</b>	184116
<b>PRODUCT LENGTH/DEPTH</b>	100 mm
<b>PRODUCT HEIGHT</b>	100 mm
<b>PRODUCT WIDTH</b>	100 mm
<b>PRODUCT WEIGHT</b>	0.023 kg
<b>COMPLIANCES</b>	RoHS conform

<b>USED WITH</b>	IZMX16..., IZMX40...
<b>ELECTRIC CONNECTION TYPE</b>	Flat plug-in connection
<b>RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V</b>	10 A
<b>MOUNTING METHOD</b>	Other
<b>ACCESSORY/SPARE PART TYPE</b>	Trip indication / Reset options
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)</b>	2
<b>NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>MODEL</b>	Integrable
<b>TYPE</b>	Accessory
<b>SPECIAL FEATURES</b>	"Triggered" signaling contact with two changeover contacts
<b>RATED BREAKING CAPACITY (INDUCTIVE LOAD)</b>	0.25 A (250 V DC) 0.5 A (125 V DC) 10 A (250 V AC)

<a href="#">eaton-izmx16-izmx40-uvr-st-ots-il0131087en-z.pdf</a>
<a href="#">eaton-circuit-breaker-izmx-inx-auxiliary-switch-3d-drawing-010.eps</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

