

Eaton 184214

Eaton Moeller series IZMX/INX - ACB.
Mechanical interlock, TYPE 32, bowden
cables, W

PRODUCT NAME	Eaton Moeller series IZMX/INX mechanical interlock
CATALOG NUMBER	184214
PRODUCT LENGTH/DEPTH	457.2 mm
PRODUCT HEIGHT	203.2 mm
PRODUCT WIDTH	457.2 mm
PRODUCT WEIGHT	1.149 kg
COMPLIANCES	RoHS conform

USED WITH	IZMX16...W INX16...W
MOUNTING METHOD	Withdrawable
ACCESSORY/SPARE PART TYPE	Withdrawable units
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
TYPE	Accessory

SPECIAL FEATURES

- For 3 circuit breakers: Two normal incoming units (A, C) and one coupling (B). Any one or two switches can be closed at the same time. Three cable kits are required in addition.
- Type 32

eaton-izmx16-drawout-cable-interlock-kit-il0131080en-us.pdf	
eaton-circuit-breaker-izmx-inx-acb-dimensions-002.eps	
eaton-circuit-breaker-izmx-inx-acb-3d-drawing-005.eps	

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

