



Eaton 185139

Eaton Moeller® series C22 Indicator light,
Flat, Cable (black) with non-terminated end,
4 pole, 1 m, Lens Blue, LED Blue, 24 V AC/DC

□□□□

PRODUCT NAME	Eaton Moeller® series C22 Indicator light
CATALOG NUMBER	185139
PRODUCT LENGTH/DEPTH	1061 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.046 kg
CERTIFICATIONS	UL IEC/EN 60947-5-1 CE VDE 0660 CSA



Powering Business Worldwide

□□□□

TYPE	Indicator lights
PRODUCT CATEGORY	RMQ compact solution
ELECTRIC CONNECTION TYPE	Other
FITTED WITH:	Light source Front ring
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	800 V AC
BEZEL COLOR	Other
CABLE MATERIAL	PUR
LAMP SOCKET TYPE	LED
ACTUATOR DIAMETER	4.7 mm
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
NUMBER OF PILOT LIGHTS	1
OPENING DIAMETER	22.5 mm
OPENING HEIGHT	0 mm
RATED INSULATION VOLTAGE (UI)	30 V
RATED OPERATIONAL VOLTAGE (UE) - MAX	24 V
BEZEL MATERIAL	Plastic
DEGREE OF PROTECTION	IP Other NEMA Other
LENS COLOR	Blue
VOLTAGE TYPE	AC/DC
DESIGN	Cable end open Flat
MOUNTING POSITION	As required
LIGHT COLOR	Blue
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
RATED OPERATIONAL VOLTAGE (UE) - MIN	24 V

□□

DECLARATIONS OF CONFORMITY	eaton-pushbutton-declaration-of-conformity-uk250928en.pdf
□□□□□	IL047016ZU
□□□	eaton-operating-c22-indicator-light-wiring-diagram-003.eps
□□	eaton-operating-c22-indicator-light-dimensions-003.eps eaton-operating-button-symbol-003.eps eaton-operating-c22-pushbutton-3d-drawing.eps

WIDTH OPENING	0 mm
OVERVOLTAGE CATEGORY	III
CABLE LENGTH	1 m
CONNECTION TYPE	Cable (black) with non-terminated end, 4 pole
LENS TYPE	Round Flat
SHOCK RESISTANCE	30 g, Mechanical, Shock duration 11 ms
RATED OPERATIONAL VOLTAGE	24 V AC/DC (LED)
SHORT-CIRCUIT PROTECTION RATING	Max. 4 A gG/gL, Fuse, Contacts
TIGHTENING TORQUE	2 Nm, Threaded ring

□□□□:
□□□□:
□□□:
□□: