



Eaton 185953

Eaton Moeller® series C30 Indicator light, Flat, Cable (black) with non-terminated end, 4 pole, 1 m, Lens Red, LED Red, 24 V AC/DC

□□□□

PRODUCT NAME	Eaton Moeller® series C30 Indicator light
CATALOG NUMBER	185953
PRODUCT LENGTH/DEPTH	1060 mm
PRODUCT HEIGHT	46 mm
PRODUCT WIDTH	36 mm
PRODUCT WEIGHT	0.063 kg
CERTIFICATIONS	IEC/EN 60947-5-1 VDE 0660



Powering Business Worldwide

□□□□

TYPE	Indicator lights
PRODUCT CATEGORY	RMQ compact solution
ELECTRIC CONNECTION TYPE	Other
FITTED WITH:	Light source Front ring
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	800 V AC
BEZEL COLOR	Chrome
CABLE MATERIAL	PUR
LAMP SOCKET TYPE	LED
ACTUATOR DIAMETER	4.7 mm
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
NUMBER OF PILOT LIGHTS	1
OPENING DIAMETER	30 mm
RATED INSULATION VOLTAGE (UI)	30 V
RATED OPERATIONAL VOLTAGE (UE) - MAX	24 V
BEZEL MATERIAL	Metal
DEGREE OF PROTECTION	IP Other NEMA Other
LENS COLOR	Red
VOLTAGE TYPE	AC/DC
DESIGN	Flat Cable end open
MOUNTING POSITION	As required
LIGHT COLOR	Red
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
RATED OPERATIONAL VOLTAGE (UE) - MIN	24 V
OVERVOLTAGE	III

□□

DECLARATIONS OF CONFORMITY	eaton-pushbutton-declaration-of-conformity-uk250928en.pdf
□□□□□	IL047021ZU
□□□	eaton-operating-c22-indicator-light-wiring-diagram-003.eps
□□	eaton-operating-c30-indicator-light-dimensions-002.eps eaton-operating-c30-indicator-light-3d-drawing-002.eps

