

Eaton 185978

Eaton Moeller® series C30 Illuminated pushbutton actuator, Flat, momentary, 1 N/O, Cable (black) with non-terminated end, 4 pole, 3.5 m, LED green, green, Blank, 24 V AC/DC, Metal bezel

PRODUCT NAME	Eaton Moeller® series C30 Illuminated pushbutton actuator
CATALOG NUMBER	185978
PRODUCT LENGTH/DEPTH	3560 mm
PRODUCT HEIGHT	46 mm
PRODUCT WIDTH	36 mm
PRODUCT WEIGHT	0.142 kg
CERTIFICATIONS	IEC/EN 60947-5-1 VDE 0660 CSA Class No.: 321103 CSA File No.: 165628 UL 508 CSA-C22.2 No. 14-18 and No. 94.2-15 CE marking UL Category Control No.: NKCR UL File No.: E29184 UL CSA

TYPE	Illuminated pushbutton actuator
ACTUATOR COLOR	Green
ACTUATOR FUNCTION	Momentary Spring-return
ELECTRIC CONNECTION TYPE	Cable
FITTED WITH:	Front ring
OPERATING FREQUENCY	3600 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	800 V AC
BEZEL COLOR	Chrome
CABLE MATERIAL	PUR
ACTUATING FORCE	5 N
ACTUATOR DIAMETER	29.7 mm
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
LAMP VOLTAGE - MAX	24 V
NUMBER OF COMMAND POSITIONS	1
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
BEZEL MATERIAL	Metal
DESIGN	Cable end open Flat
MOUNTING POSITION	As required
LIGHT COLOR	Green
RATED CONDITIONAL	1 kA

IL047021ZU	
eaton-operating-c22-wiring-diagram.eps	
eaton-operating-diagram-contact-travel-diagram.eps	
eaton-operating-c30-pushbutton-dimensions-003.eps	
eaton-operating-c30-pushbutton-3d-drawing.eps	
eaton-operating-button-symbol-004.eps	

SHORT-CIRCUIT CURRENT (IQ)	
CONNECTION TYPE	Cable (black) with non-terminated end, 4 pole
CABLE LENGTH	3.5 m
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	1 failure per 17,000,000 swtching operations (statistically determined, at 17 V DC/7 mA: N/O contact
DEGREE OF PROTECTION	NEMA Other IP67/IP69K
INSCRIPTION	Blank
FRONT ELEMENT TYPE	Flat
LENS TYPE	Round
RATED OPERATIONAL VOLTAGE	24 V AC/DC (LED)
SHOCK RESISTANCE	30 g, Mechanical, Shock duration 11 ms
SHORT-CIRCUIT PROTECTION RATING	Max. 4 A gG/gL, Fuse, Contacts
OPENING DIAMETER	30.5 mm
OPENING HEIGHT	0 mm
RATED INSULATION VOLTAGE (UI)	30 V
RATED OPERATIONAL CURRENT (IE) AT AC-15, 24 V	4 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V	3 A
WIDTH OPENING	0 mm
PRODUCT CATEGORY	RMQ compact solution
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-30 °C
TIGHTENING TORQUE	2 Nm, Threaded ring
SUITABLE FOR	Illumination

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

