



Eaton 186098

Eaton Moeller® series C22 Changeover switch, With thumb-grip, momentary, 1 N/O, Cable (black) with M12A plug, 4 pole, 0.2 m, 2 positions, Bezel: titanium



| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Moeller® series C22 Changeover switch |
| CATALOG NUMBER | 186098 |
| PRODUCT LENGTH/DEPTH | 276 mm |
| PRODUCT HEIGHT | 30 mm |
| PRODUCT WIDTH | 30 mm |
| PRODUCT WEIGHT | 0.035 kg |
| CERTIFICATIONS | CSA CE VDE 0660 UL IEC/EN 60947-5-1 CSA File No.: 165628 CSA Class No.: 321103 UL File No.: E29184 UL 508 CSA-C22.2 No. 14-18 and No. 94.2-15 CE marking UL Category Control No.: NKCR UL listed, CSA certified |



Powering Business Worldwide

□□□□

| | |
|--|--|
| TYPE | Selector switch actuator |
| ACTUATOR COLOR | Black |
| PRODUCT CATEGORY | RMQ compact solution |
| ACTUATOR FUNCTION | Spring-return Momentary |
| ELECTRIC CONNECTION TYPE | Other |
| FITTED WITH: | Front ring |
| OPERATING FREQUENCY | 2000 Operations/h |
| POLLUTION DEGREE | 3 |
| CLIMATIC PROOFING | Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78 |
| CONNECTION TO SMARTWIRE-DT | No |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) | 800 V AC |
| ACTUATOR TYPE | Toggle |
| ACTUATOR DIAMETER | 4.7 mm |
| AMBIENT OPERATING TEMPERATURE - MAX | 70 °C |
| AMBIENT OPERATING TEMPERATURE - MIN | -30 °C |
| NUMBER OF CONTACTS (CHANGE-OVER CONTACTS) | 0 |
| NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS) | 0 |
| NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS) | 1 |
| OPENING DIAMETER | 22.5 mm |
| OPERATING TORQUE | 0.3 Nm |
| RATED INSULATION VOLTAGE (UI) | 250 V |
| RATED OPERATIONAL CURRENT (IE) AT AC-15, 24 V | 4 A |
| RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V | 3 A |
| BEZEL COLOR | Titanium |
| CABLE MATERIAL | PUR |
| BEZEL MATERIAL | Plastic |

□□

| | |
|-----------------------------------|---|
| DECLARATIONS OF CONFORMITY | eaton-pushbutton-declaration-of-conformity-uk250928en.pdf |
| □□□□□ | IL047016ZU |
| □□□ | eaton-operating-pushbutton-wiring-diagram-007.eps |
| □□□□□ | eaton-operating-diagram-contact-travel-diagram.eps |
| | eaton-operating-changeover-switch-dimensions.eps |
| □□ | eaton-operating-changeover-switch-3d-drawing-002.eps |

