



□□□□

Eaton 186263

Eaton Moeller® series C22 Key-operated actuator, RMQ compact solution, maintained, 1 N/O, Cable (black) with non-terminated end, 4 pole, 1 m, 2 positions, MS1, Bezel: titanium

□□□□

PRODUCT NAME	Eaton Moeller® series C22 Key-operated actuator
CATALOG NUMBER	186263
PRODUCT LENGTH/DEPTH	1097 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.069 kg
CERTIFICATIONS	UL VDE 0660 CE CSA IEC/EN 60947-5-1 CSA File No.: 165628 CSA Class No.: 321103 UL File No.: E29184 UL 508 CSA-C22.2 No. 14-18 and No. 94.2-15 CE marking UL Category Control No.: NKCR UL listed, CSA certified
CATALOG NOTES	Not suitable for master key systems



Powering Business Worldwide

□□□□

TYPE	Key-operated button
ACCESSORIES	1 key included with supplied equipment.
ACTUATOR COLOR	Black
PRODUCT CATEGORY	RMQ compact solution
ACTUATOR FUNCTION	Switching function latching Key withdrawable in position 1 Maintained Key withdrawable in position 0
ELECTRIC CONNECTION TYPE	Other
FITTED WITH:	Front ring
OPERATING FREQUENCY	100 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	800 V AC
ACTUATOR TYPE	Key
ACTUATOR DIAMETER	4.7 mm
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
OPENING DIAMETER	22.5 mm
OPERATING TORQUE	0.5 Nm
RATED INSULATION VOLTAGE (UI)	250 V
RATED OPERATIONAL CURRENT (IE) AT AC-15, 24 V	4 A

□□

DECLARATIONS OF CONFORMITY	eaton-pushbutton-declaration-of-conformity-uk250928en.pdf
□□□□□	IL047016ZU
□□□	eaton-operating-c22-pushbutton-wiring-diagram-002.eps
□□□□□	eaton-operating-diagram-contact-travel-diagram.eps
□□	eaton-operating-c22-key-operated-actuator-dimensions.eps eaton-operating-c22-key-operated-actuator-3d-drawing.eps

