

Eaton 187080

Eaton Moeller® series M30 Potentiometer,
flat front, M30, 30.5 mm, Metal bezel

PRODUCT NAME	Eaton Moeller® series M30 Potentiometer
CATALOG NUMBER	187080
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	48 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	0.05 kg
CERTIFICATIONS	IEC/EN 60947
CATALOG NOTES	Front element SmartWire- DT potentiometer

TYPE	Potentiometer
ACCESSORY/SPARE PART TYPE	Other
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	Yes
BEZEL COLOR	Metal
DESIGN	Flat front
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP65
FUNCTIONS	For connecting to SmartWire-DT
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
OPENING DIAMETER	30.5 mm

IL047030ZU	
eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf	
eaton-operating-m30-potentiometer-wiring-diagram.eps	
eaton-operating-m30-potentiometer-dimensions-002.eps	
eaton-operating-m30-potentiometer-3d-drawing-002.eps	
/	RMQ small E-Stop emergency-stop button

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.