



□□□□□

Eaton 193178

Eaton xEnergy Basic LV systems Low voltage switchgear. Surface-mounted installation distributor IP31, EP, WxHxD=850x1460x250mm, white, twist lock

□□□□

PRODUCT NAME	Eaton xEnergy Basic empty enclosure
CATALOG NUMBER	193178
PRODUCT LENGTH/DEPTH	250 mm
PRODUCT HEIGHT	1460 mm
PRODUCT WIDTH	850 mm
PRODUCT WEIGHT	38.2 kg
COMPLIANCES	RoHS conform

□□□□

TYPE	Basic device
FEATURES	Mounting plate depth-adjustable EMC-version Connectable
SURFACE FINISHING	Powder coating
DEGREE OF PROTECTION	IP31 IK08 (impact resistance) Other
GRADE MATERIAL	Sheet steel
MATERIAL QUALITY	Other
COLOR	White
PERMISSIBLE LOAD OF THE MOUNTING PLATE ACCORDING TO IEC 62208 - MAX	0 N
NUMBER OF LOCKS	0
RAL-NUMBER	9016
MATERIAL	Steel Sheet steel
MOUNTING METHOD	Wall fastening Surface mounting
FUNCTIONS	Basic device
INSTALLATION TYPE	Floor standing wall model
NUMBER OF COVERS/DOORS	1
SUITABLE FOR	Metrical mounting
PERMISSIBLE LOAD OF THE ENCLOSURE ACCORDING TO IEC 62208 - MAX	0 N
PERMISSIBLE LOAD OF THE DOOR(S) ACCORDING TO IEC 62208 - MAX	0 N
THERMAL DISSIPATION (DELTA T = 20 K) ACCORDING TO IEC/TR 60890	0 W
NUMBER OF CONNECTOR HOLES	0

□□

MCAD MODEL [bp_o_850_14_ep_w.stp](#)
[bp_o_850_14_ep_w.dwg](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

