



Eaton 195333

Eaton xEnergy Basic LV systems Low voltage switchgear. Terminal block 2x35mm², 270A Cu / 240A Al

□□□□

PRODUCT NAME	Eaton xEnergy Basic other accessory
CATALOG NUMBER	195333
PRODUCT LENGTH/DEPTH	45.6 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	43.2 g
COMPLIANCES	RoHS conform



Powering Business Worldwide

FUNCTIONS	Additional equipment
CONDUCTOR CROSS SECTION (FLEXIBLE, FINE-STRAND) WITH CABLE END SLEEVE - MAX	25 mm²
CONDUCTOR CROSS SECTION (FLEXIBLE, FINE-STRAND) WITH CABLE END SLEEVE - MIN	25 mm²
CONDUCTOR CROSS SECTION (SOLID, SOLID-STRAND) - MAX	35 mm²
CONDUCTOR CROSS SECTION (SOLID, SOLID-STRAND) - MIN	35 mm²
AMPERAGE RATING	270 A
NUMBER OF POLES	Single-pole
NUMBER OF CLAMP POSITIONS PER POLE	2

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: