



□□□□

Eaton 198284

Eaton Moeller® series Rapid Link 1.5-m adapter cable C2 Q4/2

□□□□

PRODUCT NAME	Eaton Rapid Link Adapter cable
CATALOG NUMBER	198284
PRODUCT LENGTH/DEPTH	1.68 m
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	50 mm
PRODUCT WEIGHT	0.44 kg
COMPLIANCES	CE



Powering Business Worldwide



FEATURES	Connector system system-oriented Oil resistant (acc. EN 60811-404)
FITTED WITH:	Protective conductor
CONNECTION 1	Other
CONNECTION 2	Other
DEGREE OF PROTECTION	Other
EURO CLASS ACIDITY (EN 13501-6)	None
EURO CLASS FLAMING DROPLETS/PARTICLES (EN 13501-6)	None
OUTER SHEATH COLOR	Gray
REACTION-TO-FIRE CLASS (EN 13501-6)	None
SPIRALIZED CABLE	No
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
NOMINAL CROSS SECTION (CONDUCTOR)	1.5 mm ²
NOMINAL CURRENT	6.6 A
NOMINAL VOLTAGE - MAX	480 V
NOMINAL VOLTAGE - MIN	380 V
NUMBER OF CORES	5
OUTER DIAMETER - APPROXIMATE	10 mm
PERMISSIBLE AMBIENT TEMPERATURE - MAX	55 °C
PERMISSIBLE AMBIENT TEMPERATURE - MIN	-10 °C
OUTER SHEATH MATERIAL	Other
SMOKE DEVELOPMENT CLASS (EN 13501-6)	None
CABLE ENTRY CONNECTION 1	Straight
CABLE ENTRY CONNECTION 2	Straight



DECLARATIONS OF CONFORMITY	eaton-accessory-declaration-of-conformity-uk251005en.pdf
	eaton-rapid-link-5-brochure-br040014en-en-us.pdf

