



Eaton 200MJ28-8

Eaton Bussmann series low voltage british standard fuse, 200A, AC 415 V, V88/J, 31 x 112 mm, gU, type 8

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	200MJ28-8
PRODUCT LENGTH/DEPTH	129.8 mm
PRODUCT HEIGHT	48.9 mm
PRODUCT WIDTH	37.9 mm
PRODUCT WEIGHT	151.8 g
COMPLIANCES	CE CE Marked RoHS Compliant
CERTIFICATIONS	BS IEC 60269 EAC



Powering Business Worldwide

□□□□

AMPERAGE RATING	200 A
CURRENT TYPE	AC
BREAKING CAPACITY	80 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	MJ28
UTILIZATION CATEGORY	gU (utility/distribution protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	13 W
CONNECTION	Bolt-on
CONSTRUCTION	BS88/J
CONSTRUCTION SIZE	J
FUSE SHAPE	Dual slotted bolted tags
VOLTAGE TYPE	AC
MATERIAL	Ceramic body
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	feeder pillars
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other
RATED SWITCHING CAPACITY AC	80 kA

□□

