


Eaton 200MJ30-7

Eaton Bussmann series low voltage british standard fuse, 200A, AC 415 V, V88/J, 31 x 110 mm, gU, 82mm fixing centres, type 7

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	200MJ30-7
UPC	051712531498
PRODUCT LENGTH/DEPTH	111 mm
PRODUCT HEIGHT	31 mm
PRODUCT WIDTH	31 mm
PRODUCT WEIGHT	158.5 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS IEC 60269 EAC

AMPERAGE RATING	200 A
FITTED WITH:	Slotted tags
CURRENT TYPE	AC
MOUNTING DIMENSION	Other
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	82 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
CLASS	Other
FUSE TYPE	MJ30
UTILIZATION CATEGORY	gU (utility/distribution protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	13 W
CONNECTION	Bolt-on
CONSTRUCTION	BS88/J
CONSTRUCTION SIZE	J
FUSE SHAPE	Dual slotted bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	feeder pillars
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

