



Eaton 200MJ31-7

Eaton Bussmann series low voltage british standard fuse, 200A, AC 415 V, V88/J, 31 x 131 mm, gU, type 7

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	200MJ31-7
UPC	051712555821
PRODUCT LENGTH/DEPTH	160 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	236.8 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	BS IEC 60269 EAC



Powering Business Worldwide

AMPERAGE RATING 200 A

FITTED WITH: Slotted tags

CURRENT TYPE AC

MOUNTING DIMENSION Other

**CENTER-TO-CENTER
DISTANCE OF
CONNECTIONS** 92 mm

BREAKING CAPACITY	80 kA
--------------------------	-------

RATED SWITCHING CAPACITY	80 kA
---------------------------------	-------

RATED VOLTAGE AC 415 V

CLASS Class gG/gL

FUSE TYPE MJ31

UTILIZATION CATEGORY	gU (utility/distribution protection)
----------------------	--------------------------------------

COLOR None

INTERRUPT RATING 80 kAIC

FUSE INDICATOR	None
-----------------------	------

INSULATED METAL GRIPPING LUGS (IMGL)	No
--------------------------------------	----

WATT LOSSES 13 W

CONNECTION Bolt-on

CONSTRUCTION BS88/J

CONSTRUCTION SIZE J

FUSE SHAPE Dual slotted bolted tags

VOLTAGE TYPE	AC
--------------	----

VOLTAGE RATING 415 V

TYPE	Fuse
-------------	------

APPLICATION feeder pillars

**FUSE SYSTEM
(ACCORDING TO IEC
60269)**

11

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk251033en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

