



□□□□□

Eaton 207189

Eaton Moeller® series T3

Changeoverswitches, T3, 32 A, surface mounting, 3 contact unit(s), Contacts: 6, 60 °, maintained, With 0 (Off) position, 0-1-2, Design number 8451

□□□□

PRODUCT NAME	Eaton Moeller® series T3 Changeover switch
CATALOG NUMBER	207189
PRODUCT LENGTH/DEPTH	181 mm
PRODUCT HEIGHT	127 mm
PRODUCT WIDTH	100 mm
PRODUCT WEIGHT	0.563 kg
CERTIFICATIONS	CSA Class No.: 3211-05 CSA file No. 012528 IEC/EN 60947-3 IEC/EN 60947 VDE 0660 IEC/EN 60204 CSA UL UL 60947-4-1 CSA-C22.2 No. 60947-4-1-14 CSA-C22.2 No. 94 CE marking UL Category Control No.: NLRV UL File No.: E36332 UL Listed CSA certified



Powering Business Worldwide

□□□□

TYPE	Changeover switch
FEATURES	Complete device in housing
FITTED WITH:	0 (off) position
ENCLOSURE MATERIAL	Plastic
ACTUATOR TYPE	Short thumb-grip
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
NUMBER OF POLES	3
DEGREE OF PROTECTION	IP65 NEMA 1 NEMA 12
MODEL	Reverser
DEGREE OF PROTECTION (FRONT SIDE)	IP65 NEMA 12
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	23.7 A
SUITABLE FOR	Ground mounting Front mounting
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	15 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	12 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
RATED UNINTERRUPTED CURRENT (IU)	32 A

□□

DECLARATIONS OF CONFORMITY	eaton-changeover-switch-declaration-of-conformity-uk251329en.pdf
□□□□□	IL03801008Z2021_06.pdf
□□□	eaton-rotary-switches-switch-t0-changeover-switch-wiring-diagram-009.eps
□□	eaton-rotary-switches-front-plate-t0-step-switch-symbol-006.eps

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

