

Eaton 20D27

Eaton Bussmann series low voltage D fuse, 500V, 20A, 50 kAIC, Non Indicating, fuse, Class C gL/gG, Time delay, Blue, Ceramic body

PRODUCT NAME	Eaton Bussmann series low voltage D fuse
CATALOG NUMBER	20D27
UPC	051712832335
PRODUCT LENGTH/DEPTH	50 mm
PRODUCT HEIGHT	21.5 mm
PRODUCT WIDTH	21.5 mm
PRODUCT WEIGHT	29.64 g
COMPLIANCES	CE Marked GoST-R RoHS Compliant
CERTIFICATIONS	IEC 60269 VDE DIN EN 60269-3 (VDE 0636 Part 30) DIN EN 60269-1 (VDE 0636 Part 10) DIN VDE 0636-301

AMPERAGE RATING	20 A
FUSE SIZE	DII
BREAKING CAPACITY	50 kA
CONSTRUCTION SIZE (FUSE INSERTS)	DII
RATED VOLTAGE AC	500 V
CLASS	Class C gL/gG
FUSE TYPE	D27 -Time delay
ACCESSORY/SPARE PART TYPE	20GD27 Blue screw cap gauge piece
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	Blue
INTERRUPT RATING	50 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Other
CONSTRUCTION	D2
CONSTRUCTION SIZE	DII
FUSE SHAPE	Bottle
RESPONSE TIME	Time-delay
SUITABLE FOR	E27/DII Fuse base TFD27 Fuse base screw fixing SFRD27 Fuse base DIN-Rail mount TFRD27 Fuse base DIN-Rail mount
MATERIAL	White ceramic body
RELEASE CHARACTERISTIC	Time-lag
QUANTITY	25
VOLTAGE RATING	500 V
TYPE	fuse
APPLICATION	For domestic and general industrial applications



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

