



Eaton 20D27R

Eaton Bussmann series low voltage D fuse, Ultra-rapid, 500V, 20A, Non Indicating, fuse, Class gR, Time delay, Blue, Ceramic body

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage D fuse
CATALOG NUMBER	20D27R
UPC	051712832359
PRODUCT LENGTH/DEPTH	50 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	30.12 g
COMPLIANCES	CE Marked GoST-R RoHS Compliant
CERTIFICATIONS	IEC 60269 VDE DIN EN 60269-3 (VDE 0636 Part 30) DIN EN 60269-1 (VDE 0636 Part 10) DIN VDE 0636-301



Powering Business Worldwide

□□□□

AMPERAGE RATING	20 A
FUSE SIZE	DII
BREAKING CAPACITY	50 kA
CONSTRUCTION SIZE (FUSE INSERTS)	DII
RATED VOLTAGE AC	500 V
CLASS	Class gR
FUSE TYPE	D27R - Ultra rapid
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
ACCESSORY/SPARE PART TYPE	20GD27 Blue screw cap gauge piece
COLOR	Blue
INTERRUPT RATING	50 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Other
CONSTRUCTION	D2
CONSTRUCTION SIZE	DII
FUSE SHAPE	Bottle
RESPONSE TIME	Ultra rapid
SUITABLE FOR	E27/DII Fuse base TFD27 Fuse base screw fixing SFRD27 Fuse base DIN-Rail mount TFRD27 Fuse base DIN-Rail mount
MATERIAL	White ceramic body
RELEASE CHARACTERISTIC	Super fast (FF)
QUANTITY	25
VOLTAGE RATING	500 V
TYPE	fuse
SPECIAL FEATURES	Ultra-rapid
APPLICATION	For domestic and general industrial applications

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-d-fuse-declaration-of-conformity-uk251016en.pdf](#)

