



Eaton 20LCTF

Fuse-link, high speed, 20 A, AC 240 V, DC 150 V, BS88, 9 x 27 mm, aR, BS

□□□□

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	20LCTF
PRODUCT LENGTH/DEPTH	52 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	84 mm
PRODUCT WEIGHT	5.25 g
COMPLIANCES	CE



Powering Business Worldwide

□□□□

AMPERAGE RATING	20 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	240 V
RATED VOLTAGE DC	150 V
MOUNTING DIMENSION	Other
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I ₂ T)	160
WATT LOSSES	4 W
FUSE SHAPE	Cylindrical
PRE ARC (I ₂ T)	25
COLOR	None
INTERRUPT RATING	200 kA RMS Sym, 50 kA DC at 150 Vdc
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	240 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	LCTF
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250922en.pdf](#)

