

Eaton 20NHM000B

Eaton Fuse-link, low voltage, 20 A, AC 500 V, NH000, aM, IEC, dual indicator


PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	20NHM000B
PRODUCT LENGTH/DEPTH	125 mm
PRODUCT HEIGHT	58 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	131 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620



AMPERAGE RATING	20 A
FITTED WITH:	Insulated metal gripping lugs
FUSE SIZE	NH03
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	aM (switchgear protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	Yes
WATT LOSSES	0.9 W
CONNECTION	Blade end
CONSTRUCTION	NH000
CONSTRUCTION SIZE	NH000
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	Microswitch BVL50
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	500 V
TYPE	Fuse

APPLICATION	• industrial • Utilities, Solar, Wind
-------------	---

RATED SWITCHING CAPACITY AC	120 kA
-----------------------------	--------



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

