

Eaton 215639

Eaton Moeller series xPole - Busbar. EV
busbars 3Ph., 12HP, 63A for PLS. CLS. PKN.,
PFIM, PFHM, PFNM

PRODUCT NAME	Eaton Moeller series busbar
CATALOG NUMBER	215639
PRODUCT LENGTH/DEPTH	210 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	10 mm
PRODUCT WEIGHT	0.089 kg
COMPLIANCES	RoHS conform

USED WITH	EVG Busbar
TYPE	• Busbar • EVG
FEATURES	Insulated
ACCESSORY/SPARE PART TYPE	Busbar for residual current circuit breakers Busbar for miniature circuit breaker Busbar for combined residual current/power circuit breaker
ELECTRIC CONNECTION TYPE	Fork
RATED SURGE VOLTAGE	4 kV
RATED UNINTERRUPTED CURRENT (IU)	63 A
SUITABLE FOR NUMBER OF DEVICES	4
NUMBER OF POLES	Three-pole
COLOR	Other
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
CROSS SECTION	10 mm ²
NUMBER OF MODULAR SPACINGS	12
NUMBER OF PHASES	3
PITCH DIMENSIONS	0 mm
RATED OPERATIONAL VOLTAGE (UE) - MAX	500 V
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	25 kA
FUNCTIONS	Busbar
SUITABLE FOR	4 devices

eaton-busbar-3d-drawing.jpg	

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

