

## Eaton 219723

Eaton xComfort KLV LV systems Final  
Distribution Boards. KL-4 terminal bar, 1 x  
25 mm<sup>2</sup> + 3 x 16 mm<sup>2</sup>, max. 63 A

PRODUCT NAME	Eaton xComfort KLV screw-type terminal
CATALOG NUMBER	219723
PRODUCT LENGTH/DEPTH	7 mm
PRODUCT HEIGHT	9 mm
PRODUCT WIDTH	36 mm
PRODUCT WEIGHT	0.015 kg
COMPLIANCES	RoHS conform

<b>USED WITH</b>	Individual KL screw terminal
	KLV distribution board
	BF flat distribution board
	Accessory consideration
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• Additional equipment</li> <li>• BF flat distribution board</li> <li>• KLV distribution board</li> </ul>
<b>ACCESSORY/SPARE PART TYPE</b>	General
<b>COLOR</b>	Other
<b>NOMINAL CURRENT</b>	63 A
<b>NUMBER OF POLES</b>	Single-pole
<b>CONNECTION TYPE</b>	Clamp Screwing
<b>MATERIAL</b>	Metal
<b>MOUNTING METHOD</b>	Screw
<b>SUITABLE FOR</b>	Fine strand conductors Solid conductors Stranded conductors
<b>FUNCTIONS</b>	Additional equipment
<b>CONDUCTOR CROSS SECTION, INPUT - MIN</b>	1.5 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION, OUTPUT AWG - MIN</b>	0 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION, INPUT - MAX</b>	25 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION, INPUT AWG - MAX</b>	0 mm <sup>2</sup>
<b>NUMBER OF INPUTS</b>	2
<b>CONDUCTOR CROSS SECTION, INPUT AWG - MIN</b>	0 mm <sup>2</sup>
<b>NUMBER OF OUTPUTS</b>	2
<b>CONDUCTOR CROSS SECTION, OUTPUT - MAX</b>	16 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION, OUTPUT AWG - MAX</b>	0 mm <sup>2</sup>
<b>CONDUCTOR CROSS</b>	1.5 mm <sup>2</sup>

[eaton-xcomfort-compact-distribution-boxes-brochure-br014015en-en-us.pdf](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

