



Eaton 219724

Eaton xComfort KLV LV systems Final
Distribution Boards. KL-7 terminal bar, 1 x
25 mm² + 6 x 16 mm², max. 63 A

□□□□

PRODUCT NAME	Eaton xComfort KLV screw-type terminal
CATALOG NUMBER	219724
PRODUCT LENGTH/DEPTH	7 mm
PRODUCT HEIGHT	9 mm
PRODUCT WIDTH	57 mm
PRODUCT WEIGHT	0.028 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

USED WITH

Individual KL screw
terminal
BF flat distribution board
Accessory consideration
KLV distribution board

TYPE

- Additional equipment
- BF flat distribution board
- KLV distribution board

ACCESSORY/SPARE PART TYPE

General

COLOR

Other

NOMINAL CURRENT

63 A

NUMBER OF POLES

Single-pole

CONNECTION TYPE

Clamp
Screwing

MATERIAL

Metal

MOUNTING METHOD

Screw

SUITABLE FOR

Fine strand conductors
Solid conductors
Stranded conductors

FUNCTIONS

Additional equipment

CONDUCTOR CROSS SECTION, INPUT - MIN

1.5 mm²

CONDUCTOR CROSS SECTION, OUTPUT AWG - MIN

0 mm²

CONDUCTOR CROSS SECTION, INPUT - MAX

25 mm²

CONDUCTOR CROSS SECTION, INPUT AWG - MAX

0 mm²

NUMBER OF INPUTS

1

CONDUCTOR CROSS SECTION, INPUT AWG - MIN

0 mm²

NUMBER OF OUTPUTS

6

CONDUCTOR CROSS SECTION, OUTPUT - MAX

16 mm²

CONDUCTOR CROSS SECTION, OUTPUT AWG - MAX

0 mm²

CONDUCTOR CROSS SECTION, OUTPUT - MIN

1.5 mm²

[eaton-xcomfort-compact-distribution-boxes-brochure-br014015en-en-us.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

