



□□□□□

Eaton 248290

Eaton Distribution parts. Undervoltage release, 400 V, non-delayed, 1HP, 1-2x2.5 mm²

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	248290
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	65.5 mm
PRODUCT WIDTH	17.5 mm
PRODUCT WEIGHT	0.104 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	EN45545-2 IEC 61373

□□□□

USED WITH	Undervoltage releases Accessory for miniature circuit breaker Accessory
ACCESSORY/SPARE PART TYPE	Undervoltage release
MOUNTING METHOD	For fitting on left to: FAZ
ADDITIONAL EQUIPMENT REQUIRED	Under voltage coil
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-5 °C
ASSEMBLY WIDTH	1 TE
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF POLES AT MAIN CONTACT UNIT - MAX	1
NUMBER OF SWITCHES (FAULT SIGNAL)	0
VOLTAGE TYPE	AC
FUNCTIONS	Under voltage coil
DEVICE FITTING	Universal
TYPE	• Accessory • Accessory for miniature circuit breaker
APPLICATION	Switchgear for industrial and advanced commercial applications
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED SWITCH CURRENT	0 A
SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX	0 A
TRIPPING TIME	Non-delayed

□□

□□□	eaton-3d-drawing-montusa1.jpg
□□	eaton-3d-drawing-mont-usa.jpg

