

## Eaton 248292

Eaton Distribution parts. Undervoltage release, 115 V, delayed 0, 4N/O, 1HP

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	248292
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	65.5 mm
PRODUCT WIDTH	17.5 mm
PRODUCT WEIGHT	0.108 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	EN45545-2 IEC 61373

<b>USED WITH</b>	Undervoltage releases Accessory for miniature circuit breaker Accessory
<b>ACCESSORY/SPARE PART TYPE</b>	Undervoltage release
<b>MOUNTING METHOD</b>	For fitting on left to: FAZ
<b>ADDITIONAL EQUIPMENT REQUIRED</b>	Under voltage coil
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-5 °C
<b>ASSEMBLY WIDTH</b>	1 TE
<b>NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)</b>	1
<b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>	1
<b>NUMBER OF POLES AT MAIN CONTACT UNIT - MAX</b>	1
<b>NUMBER OF SWITCHES (FAULT SIGNAL)</b>	0
<b>VOLTAGE TYPE</b>	AC
<b>FUNCTIONS</b>	Under voltage coil
<b>DEVICE FITTING</b>	Universal
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• Accessory</li> <li>• Accessory for miniature circuit breaker</li> </ul>
<b>APPLICATION</b>	Switchgear for industrial and advanced commercial applications
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	115 V
<b>RATED SWITCH CURRENT</b>	0 A
<b>SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX</b>	0 A
<b>TRIPPING TIME</b>	Delayed 0.4 s

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">DA-DC-03 Z-USD</a>
	<a href="#">eaton-3d-drawing-montusa1.jpg</a>
	<a href="#">eaton-3d-drawing-mont-usa.jpg</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

