

Eaton 248294

Eaton Distribution parts. Remote tripping module, for PKNM, PKDM, PFHM-2p

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	248294
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	66 mm
PRODUCT WIDTH	9 mm
PRODUCT WEIGHT	0.05 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	EN45545-2 IEC 61373

USED WITH	Trip module
	Accessory Accessory for combined residual current/power circuit breaker
ACCESSORY/SPARE PART TYPE	Residual current release module
MOUNTING METHOD	For fitting on left to: FI/LS
ADDITIONAL EQUIPMENT REQUIRED	Remote release
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-5 °C
ASSEMBLY WIDTH	0.5 TE
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF POLES AT MAIN CONTACT UNIT - MAX	0
NUMBER OF SWITCHES (FAULT SIGNAL)	0
VOLTAGE TYPE	AC
FUNCTIONS	Remote drive
DEVICE FITTING	Other
TYPE	<ul style="list-style-type: none"> • Accessory • Accessory for combined residual current/power circuit breaker
APPLICATION	Switchgear for industrial and advanced commercial applications
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED SWITCH CURRENT	0 A
SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX	0 A

[eaton-dimensions-mas-fam.jpg](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

