



## Eaton 248432

Eaton Distribution parts. Auxiliary contact,  
1N/O+1N/C, 8 A, 250 V AC

### □□□□

<b>PRODUCT NAME</b>	Eaton Distribution parts
<b>CATALOG NUMBER</b>	248432
<b>PRODUCT LENGTH/DEPTH</b>	80 mm
<b>PRODUCT HEIGHT</b>	65.5 mm
<b>PRODUCT WIDTH</b>	8.8 mm
<b>PRODUCT WEIGHT</b>	0.04 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	EN45545-2 IEC 61373

**USED WITH** Auxiliary contacts  
Accessory for residual  
current circuit breaker  
Accessory

**ACCESSORY/SPARE PART  
TYPE** Auxiliary contacts

**MOUNTING METHOD** For fitting on left to: FI

**ADDITIONAL EQUIPMENT  
REQUIRED** Auxiliary switch

**AMBIENT OPERATING  
TEMPERATURE - MAX** 55 °C

**AMBIENT OPERATING  
TEMPERATURE - MIN** -5 °C

**ASSEMBLY WIDTH** 0.5 TE

**NUMBER OF CONTACTS  
(CHANGE-OVER  
CONTACTS)** 0

**NUMBER OF CONTACTS  
(NORMALLY CLOSED  
CONTACTS)** 1

**NUMBER OF CONTACTS  
(NORMALLY OPEN  
CONTACTS)** 1

**NUMBER OF POLES AT  
MAIN CONTACT UNIT -  
MAX** 2

**NUMBER OF SWITCHES  
(FAULT SIGNAL)** 0

**VOLTAGE TYPE** AC

**FUNCTIONS** Auxiliary switch

**DEVICE FITTING** Earth leakage switch

**TYPE**

- Accessory
- Accessory for residual current circuit breaker

**APPLICATION** Switchgear for industrial  
and advanced commercial  
applications

**RATED OPERATIONAL  
VOLTAGE (UE) - MAX** 230 V

**RATED SWITCH CURRENT** 3 A

**SUITABLE FOR CURRENT  
OF MAIN CONTACT UNIT  
- MAX** 8 A

