

Eaton 248438

Eaton Distribution parts. Shunt release, snap-fit, 12-110V AC / 12-60V DC, 50/60hz, front dimension 45 mm, mounting width 1 SU (17.5mm), top-hat rail mounting, terminal cross-section 1–25 mm²

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	248438
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	26.2 mm
PRODUCT WEIGHT	0.087 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	EN45545-2 IEC 61373

USED WITH	Shunt releases
	Accessory for combined residual current/power circuit breaker
ACCESSORY/SPARE PART TYPE	Accessory for miniature circuit breaker
	Shunt release
MOUNTING METHOD	For fitting on left to: FAZ, FRBmM-1N, Z-MS
ADDITIONAL EQUIPMENT REQUIRED	Shunt release (for power circuit breaker)
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-35 °C
ASSEMBLY WIDTH	1 TE
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF POLES AT MAIN CONTACT UNIT - MAX	1
NUMBER OF SWITCHES (FAULT SIGNAL)	0
VOLTAGE TYPE	AC
FUNCTIONS	Shunt release (for power circuit breaker)
DEVICE FITTING	Other
TYPE	<ul style="list-style-type: none"> • Accessory • Accessory for combined residual current/power circuit breaker • Accessory for miniature circuit breaker
APPLICATION	Switchgear for industrial and advanced commercial applications

DECLARATIONS OF CONFORMITY	DA-DC-03_ZP-ASA
MCAD MODEL	DA-DC-03_ZP-A
	faz_xaa.stp
	eaton-3d-drawing-mont-usa-2.jpg
	eaton-3d-drawing-zp-asa-mont.jpg

RATED OPERATIONAL VOLTAGE (UE) - MAX	24 V
RATED SWITCH CURRENT	0 A
SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX	15 A

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

